

Automation Panel - AP5000 - Swing arm

Device number key

x = wildcard
 ES = Emergency stop switch
 KS = Key switch
 PB = Pushbutton
 TS = Selector switch

	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
	Group		Automation Panel		Key/Pad Unit	Handles	Consoles / USB Hub	Flanges	Panel version	Link	Free	Free	Free	Free		Version (000 = standard)		
Automation Panel - AP5000 - Swing arm	5	A									0	0	0	0	-	0	0	0
Automation Panel swing arm mounted 15.0" (1024x768), single-touch RES (5AP5120.1505-000)			5	2														
Automation Panel swing arm mounted 19.0" (1280x1024), single-touch RES (5AP5120.1906-000)			6	2														
Automation Panel swing arm mounted 15.6" (1366x768), multi-touch PCT (5AP5130.156B-000)			B	3														
Automation Panel swing arm mounted 15.6" (1366x768), multi-touch PCT, extension (5AP5230.156B-000)			B	4														
Automation Panel swing arm mounted 18.5" (1366x768), multi-touch PCT (5AP5130.185B-000)			B	5														
Automation Panel swing arm mounted 18.5" (1366x768), multi-touch PCT, extension (5AP5230.185B-000)			B	6														
Automation Panel swing arm mounted 21.5" (1920x1080), multi-touch PCT (5AP5130.215C-000)			C	5														
Automation Panel swing arm mounted 21.5" (1920x1080), multi-touch PCT, extension (5AP5230.215C-000)			C	6														
Automation Panel swing arm mounted 24.0" (1920x1080), multi-touch PCT (5AP5130.240C-000)			C	7														
Automation Panel swing arm mounted 24.0" (1920x1080), multi-touch PCT, extension (5AP5230.240C-000)			C	8														
Automation Panel swing arm mounted 15.6" (1366x768), multi-touch PCT, FHD (5AP5130.156C-000)			C	9														
Automation Panel swing arm mounted 15.6" (1366x768), multi-touch PCT, FHD, extension (5AP5230.156C-000)			C	E														
Automation Panel swing arm mounted 18.5" (1366x768), multi-touch PCT, FHD (5AP5130.185C-000)			C	F														
Automation Panel swing arm mounted 18.5" (1366x768), multi-touch PCT, FHD, extension (5AP5230.185C-000)			C	G														
Automation Panel swing arm mounted 21.5" (1080x1920), multi-touch PCT, extension (5AP5230.215I-000)			I	2														
Without					0													
Expansion Unit - 1x ES 1x KS 2x PB 1x TS 1x USB (5ACCKP01.xxxx-000)					1													
Expansion Unit POWERLINK openSAFETY - 1x ES 1x KS 2x PB 1x TS 1x USB (5ACCKPS0.215C-000)					2													
Expansion Unit X2X openSAFETY - 1x ES 1x KS 2x PB 1x TS 1x USB (5ACCKPS1.215C-000)					3													
Expansion Unit - 1x ES 1x KS 3x PB 1x USB (5ACCKP04.xxxx-000)					4													
Expansion Cover (5ACCKP00.xxxx-000)					W													
Without					0													
Handles (5ACCHD0x.xxxx-000)					1													
Without					0													
Mounting Unit flange orientation top connect (5ACCMA00.0000-000)					1													
Mounting Unit flange orientation bottom connect (5ACCMA00.0000-000)					2													
Mounting Unit flange orientation top connect with rear USB (5ACCMA00.0001-000)					3													
Mounting Unit flange orientation bottom connect with rear USB (5ACCMA00.0001-000)					4													
Mounting Unit flange orientation top connect with USB Hub (With SDL3 the USB Hub is possible.) (5ACCMA00.0000-000) (5ACCUSB2.0002-000)					5													
Mounting Unit flange orientation bottom connect with USB Hub (With SDL3 the USB Hub is possible.) (5ACCMA00.0000-000) (5ACCUSB2.0002-000)					6													
Mounting Unit flange orientation top connect with rear USB and USB Hub (With SDL3 the USB Hub is possible.) (5ACCMA00.0001-000) (5ACCUSB2.0002-000)					7													
Mounting Unit flange orientation bottom connect with rear USB and USB Hub (With SDL3 the USB Hub is possible.) (5ACCMA00.0001-000) (5ACCUSB2.0002-000)					8													
Whithout Mounting Unit, with USB Hub (With SDL3 the USB Hub is possible.) (5ACCUSB2.0002-000)					9													
VESA Mounting Unit (5ACCMA01.0100-000)					A													
VESA Mounting Unit with USB Hub (With SDL3 the USB Hub is possible.) (5ACCMA01.0100-001) (5ACCUSB2.0002-000)					B													
Mounting Unit flange orientation top connect with 2 rear USB (5ACCMA00.0002-000)					C													
Mounting Unit flange orientation bottom connect with 2 rear USB (5ACCMA00.0002-000)					D													
Mounting Unit flange orientation top connect with 2 rear USB with USB Hub (With SDL3 the USB Hub is possible.) (5ACCMA00.0002-000) (5ACCUSB2.0002-000)					E													
Mounting Unit flange orientation bottom connect with 2 rear USB with USB Hub (With SDL3 the USB Hub is possible.) (5ACCMA00.0002-000) (5ACCUSB2.0002-000)					F													
Without					0													
Rotary Flange AP5000 (5ACCFL00.0000-000)					1													
Rotary-Tilt Flange AP5000 (5ACCFL00.0100-000)					2													
Flange adapter for Rittal flange coupling without Rittal flange coupling (5ACCFL00.0200-000)					3													
Flange adapter for Rittal flange coupling with Rittal flange coupling (5ACCFL00.0200-000) (5AC725.FLGC-00)					4													
Standard					0													
Full customized (incl. mylar versions type "I")					C													
Mylar version					F													
Industry specific					I													
Without Link					0													
Link SDL/DVI Receiver AP9x3 Einbau, AP1000 Einbau, AP5000 Tragarm (5DLSDL.1001-00)					1													
Link SDL3 Receiver AP9x3 Einbau, AP1000 Einbau, AP5000 Tragarm (5DLSL3.1001-00)					4													
Link SDL4 Receiver AP9x3 Einbau, AP1000 Einbau, AP5000 Tragarm (5DLSL4.1001-00)					A													

