

## Automation Panel - AP9x3|AP1000 - Cabinet-mounted

Device number key

	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
	Group		Automation Panel		Free	Free	Free	Free	Panel version	Link	Free	Free	Free	Free		Version (000 = standard)		
<b>Automation Panel - AP9x3/AP1000 - Cabinet-mounted</b>	5	A			0	0	0	0			0	0	0	0	-	0	0	0
Automation Panel cabinet mounted 7.0" (768x480), single-touch RES (5AP1120.0702-000)			2	A														
Automation Panel cabinet mounted 7.0" (768x480), multi-touch PCT (5AP1130.0702-000)			2	B														
Automation Panel cabinet mounted 5.7" (640x480), single-touch RES (5AP1120.0573-000)			3	A														
Automation Panel cabinet mounted 5.7" (640x480), single-touch RES, keys (5AP1151.0573-000)			3	B														
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES (5AP1120.1043-000)			3	C														
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, 22 function keys (5AP1180.1043-000)			3	D														
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, 38 function keys and 20 system keys (5AP1181.1043-000)			3	E														
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, 44 function keys and 20 system keys (5AP1182.1043-000)			3	F														
Automation Panel cabinet mounted 12.4" (800x600), single-touch RES (5AP1120.1214-000)			4	A														
Automation Panel cabinet mounted 12.1" (1024x768), single-touch RES (5AP923.1215-00)			5	A														
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES (5AP923.1505-00)			5	B														
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES (5AP1120.1505-000)			5	C														
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES, keys (5AP1180.1505-000)			5	D														
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES, 32 function keys and 92 system keys (5AP1181.1505-000)			5	E														
Automation Panel cabinet mounted 19.0" (1280x1024), single-touch RES (5AP923.1906-00)			6	A														
Automation Panel cabinet mounted 19.0" (1280x1024), single-touch RES (5AP1120.1906-000)			6	B														
Automation Panel cabinet mounted 15.6" (1366x768), multi-touch PCT (5AP933.156B-00)			B	A														
Automation Panel cabinet mounted 18.5" (1366x768), multi-touch PCT (5AP933.185B-00)			B	B														
Automation Panel cabinet mounted 15.6" (1366x768), single-touch RES (5AP1120.156B-000)			B	C														
Automation Panel cabinet mounted 21.5" (1920x1080), multi-touch PCT (5AP933.215C-00)			C	A														
Automation Panel cabinet mounted 24.0" (1920x1080), multi-touch PCT (5AP933.240C-00)			C	B														
Automation Panel cabinet mounted 18.5" (1920x1080), multi-touch PCT (5AP1130.185C-000)			C	C														
Automation Panel cabinet mounted 15.6" (1920x1080), multi-touch PCT (5AP1130.156C-000)			C	D														
Automation Panel cabinet mounted 10.1" (1280x800), single-touch RES (5AP1120.101E-000)			E	A														
Automation Panel cabinet mounted 12.1" (1280x800), single-touch RES (5AP1120.121E-000)			E	B														
Automation Panel cabinet mounted 10.1" (1280x800), multi-touch PCT (5AP1130.101E-000)			E	C														
Automation Panel cabinet mounted 12.1" (1280x800), multi-touch PCT (5AP1130.121E-000)			E	D														
Automation Panel cabinet mounted 7.0" (768x480), single-touch RES (5AP1120.0702-100)			2	A						I								
Automation Panel cabinet mounted 10.4" (640x480), single-touch RES, RFID (5AP1125.1043-100)			3	A						I								
Automation Panel cabinet mounted 10.4" (800x600), single-touch RES, RFID (5AP1125.1044-100)			4	A						I								
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES, RFID (5AP1125.1505-100)			5	A						I								
Automation Panel cabinet mounted 12.1" (1024x768), single-touch RES (5AP923.1215-100)			5	B						I								
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES (5AP923.1505-100)			5	C						I								
Automation Panel cabinet mounted 15.0" (1024x768), single-touch RES (5AP923.1505-101)			5	D						I								
Standard																		0
Full customized (incl. mylar versions type "I")																		C
Mylar version																		F
Industry specific																		I
Without Link																		0
Link SDL/DVI Receiver AP9x3 Einbau, AP1000 Einbau, AP5000 Tragarm (5DLSDL.1001-00)																		1
Link SDL3 Receiver AP9x3 Einbau, AP1000 Einbau, AP5000 Tragarm (5DLS3.1001-00)																		4
Link SDL4 Receiver AP9x3 Einbau, AP1000 Einbau, AP5000 Tragarm (5DLS4.1001-00)																		A

