

# 8BCE0015.3111A-0

## 1 General information

- UL/CSA listed
- Extremely flexible
- Assembled specifically for use with ACOPOSmulti drive systems and B&R servo motors
- speedtec - Innovative connector system for secure connections

## 2 Order data


Model number	Short description	Figure
	<b>EnDat 2.1 cables</b>	
8BCE0015.3111A-0	ACOPOSmulti EnDat 2.1 cable, length 15 m, 10x 0.14 mm <sup>2</sup> + 2x 0.5 mm <sup>2</sup> , 17-pin female speedtec EnDat connector, 15-pin male DSUB servo connector, can be used in cable drag chains, UL/CSA listed	

Table 1: 8BCE0015.3111A-0 - Order data

## 3 Technical data

Model number	8BCE0015.3111A-0
<b>General information</b>	
Cable cross section	5x 2x 0.14 mm <sup>2</sup> + 1x 2x 0.50 mm <sup>2</sup>
Durability	Oil resistance per DIN VDE 0281-1 (TM5) (HD 21.1 / DIN EN 60811-1-1/2-1) Flame resistance per IEC 60332-1-2 <sup>1)</sup>
Certification	E130266 cRUus AWM STYLE 2637 and AWM I/II A/B 90°C 30 V FT1 <sup>1)</sup>
Certifications	
CE	Yes
UL	cULus E225616 Power conversion equipment
<b>Cable construction</b>	
Supply lines	
Quantity	2
Wire insulation	PVC
Wire colors	White/Green, white/red
Design	Tinned copper stranded wire
Cross section	0.5 mm <sup>2</sup>
Shield	No
Stranding	White/Red with white/green and filler elements
Signal lines	
Quantity	10
Wire insulation	PVC
Wire colors	Blue, brown, yellow, gray, green, pink, red, black, violet, white
Design	Tinned copper stranded wire
Cross section	0.14 mm <sup>2</sup>
Shield	No
Stranding	Green with brown, gray with yellow, white with violet, black with red, pink with blue
Cable stranding	With terminating foil shield
Complete shielding	Copper braiding, optical coverage >85% and foil shield
Outer jacket	
Material	PVC
Color	Green
Labeling	B&R 5x2x0.14 + 1x2x0.5 * E130266 cURus AWM STYLE 2637 * AWM I/II A/B 90°C 30 V FT1 * <Batch number> <sup>1)</sup>
<b>Connector</b>	
Type	17-pin female speedtec EnDat connector
Connection cycles	<500
Contacts	17
Additional connectors	15-pin male DSUB servo connector Connection cycles: <200 Contacts: 15 Degree of protection per EN 60529: IP20 when connected
Degree of protection per EN 60529	IP66/67 when connected

Table 2: 8BCE0015.3111A-0 - Technical data


Model number	8BCE0015.3111A-0	
<b>Electrical characteristics <sup>1)</sup></b>		
Test voltage		
Wire/Wire		1 kV
Wire/Shield		0.8 kV
Conductor resistance		
Supply lines		≤40 Ω/km
Signal lines		≤140 Ω/km
Insulation resistance		≥20 MΩ*km
<b>Environmental conditions <sup>1)</sup></b>		
Temperature		
Moving		-20°C to +80°C
Static		-20°C to +90°C
<b>Mechanical characteristics <sup>1)</sup></b>		
Dimensions		
Length		15 m
Diameter		7.6 mm ± 0.2 mm
Bend radius		
Single bend		≥31 mm
Moving		≥62 mm
Weight		1.3 kg

Table 2: 8BCE0015.3111A-0 - Technical data

1) Values refer to the raw cable being used.

## 4 Wiring

### 4.1 Construction



Pos.	Description	Note
1	Encoder line	5x 2x 0.14 mm <sup>2</sup> + 2x 0.5 mm <sup>2</sup>
2	17-pin female circular connector	
3	DSUB housing 45°, metal-plated, 15-pin	
4	Heat shrink tubing	

Table 3: 8BCE EnDat 2.1 cables - Construction

### 4.2 Pinout



Circular connector	Pin	Description	Function	Pin	DSUB connector
	15	A	Channel A	1	
	10	COM (1, 3 - 9, 11, 13 - 15)	Encoder power supply 0 V	2	
	12	B	Channel B	3	
	7	+5 V out / 0.25 A	Encoder power supply +5 V	4	
	14	D	Data input	5	
	8	T	Clock output	8	
	16	A\	Channel A inverted	9	
	4	Sense COM	Sense input 0 V	10	
	13	B\	Channel B inverted	11	
	1	Sense +5 V	Sense input +5 V	12	
	17	D\	Data inverted	13	
	9	T\	Clock output inverted	15	

Table 4: 8BCE EnDat 2.1 cables - Pinout

### 4.3 Cable diagram




Figure 1: 8BCE EnDat 2.1 cables - Cable diagram