

8BCE0025.11120-0

1 General information

- UL/CSA listed
- Can be used in cable drag chains
- Assembled specifically for 8BCExxxx.1111A-0 EnDat 2.1 cables
- speedtec - Innovative connector system for secure connections

2 Order data


Model number	Short description	Figure
	EnDat 2.1 cables	
8BCE0025.11120-0	Cable extension for EnDat 2.1 cable with speedtec or standard connector, length 25 m, can be used in cable drag chains, UL/CSA listed	

Table 1: 8BCE0025.11120-0 - Order data

3 Technical data

Model number	8BCE0025.11120-0
General information	
Cable cross section	5x 2x 0.14 mm ² + 1x 2x 0.50 mm ²
Durability	Oil resistance per VDE 0472 Part 803 as well as standard hydraulic oils ¹⁾
Certification	UL AWM style 20963, 80°C, 30 V, E63216 and CSA AWM I/II A/B, 90°C, 30 V, FT1 LL46064 ¹⁾
Certifications	
CE	Yes
UL	cULus E225616 Power conversion equipment
Cable construction	
Supply lines	
Quantity	2
Wire insulation	Special thermoplastic material
Wire colors	White/Green, white/red
Design	Tinned copper stranded wire
Cross section	0.5 mm ²
Shield	No
Stranding	White/Red with white/green and filler elements
Signal lines	
Quantity	10
Wire insulation	Special thermoplastic material
Wire colors	Blue, brown, yellow, gray, green, pink, red, black, violet, white
Design	Tinned copper stranded wire
Cross section	0.14 mm ²
Shield	No
Stranding	Green with brown, gray with yellow, white with violet, black with red, pink with blue
Cable stranding	With terminating foil shield
Complete shielding	Copper braiding, optical coverage >85% and foil shield
Outer jacket	
Material	PUR
Color	Green, similar to RAL 6018 flat
Labeling	BERNECKER + RAINER 5x2x0.14+2x0.50 FLEX UL AWM STYLE 20963 80°C 30 V E63216 CSA AWM I/II A/B 90°C 30 V FT1 LL46064 ¹⁾
Connector	
Type	17-pin female speedtec circular connector
Connection cycles	<500
Contacts	17
Additional connectors	17-pin male coupling Connection cycles: <500 Contacts: 17 Degree of protection per EN 60529: IP67 when connected
Degree of protection per EN 60529	IP66/67 when connected
Electrical characteristics ¹⁾	
Operating voltage	≤30 V _{eff}

Table 2: 8BCE0025.11120-0 - Technical data


Model number	8BCE0025.11120-0	
Test voltage		
Wire/Wire		1 kV
Wire/Shield		0.8 kV
Conductor resistance		
Supply lines		≤40 Ω/km
Signal lines		≤140 Ω/km
Insulation resistance		>200 MΩ*km
Environmental conditions ¹⁾		
Temperature		
Moving		-20°C to +80°C
Static		-20°C to +90°C
Mechanical characteristics ¹⁾		
Dimensions		
Length		25 m
Diameter		7.85 mm ± 0.2 mm
Bend radius		
Single bend		≥24 mm
Moving		≥60 mm
Drag chain data		
Acceleration		≤6 g
Flex cycles ²⁾		>3,000,000
Speed		≤4 m/s
Weight		2 kg

Table 2: 8BCE0025.11120-0 - Technical data

- 1) Values refer to the raw cable being used.
2) At an ambient temperature of 20°C and bend radius of 65 mm.

4 Wiring

4.1 Cable construction



Pos.	Description	Note
1	Encoder line	5x 2 x 0.14 mm ² + 2 x 0.50 mm ²
2	17-pin female circular connector	
3	17-pin male coupling	

Table 3: 8BCE cable extension - Construction

4.2 Pinout



Circular connector	Pin	Description	Function	Pin	Coupling
	15	A	Channel A	15	
	10	COM (1, 3 - 9, 11, 13 - 15)	Encoder power supply 0 V	10	
	12	B	Channel B	12	
	7	+5 V out / 0.25 A	Encoder power supply +5 V	7	
	14	D	Data input	14	
	8	T	Clock output	8	
	16	A\	Channel A inverted	16	
	4	Sense COM	Sense input 0 V	4	
	13	B\	Channel B inverted	13	
	1	Sense +5 V	Sense input +5 V	1	
	17	D\	Data inverted	17	
	9	T\	Clock output inverted	9	

Table 4: 8BCE cable extension - Pinout

4.3 Cable diagram




Figure 1: 8BCE cable extension - Cable diagram