

8BCM0002.15250-0

1 General information

- Can be used in cable drag chains
- Assembled specifically for motor cables 8BCMxxxx.1523A-0 with standard size 1.5 connector
- speedtec - Innovative connector system for secure connections

2 Order data


Model number	Short description	Figure
8BCM0002.15250-0	Motor cables 10 mm² Cable extension for 10 mm ² motor cables with speedtec or standard connector, size 1.5, length 2 m, can be used in cable drag chains	

Table 1: 8BCM0002.15250-0 - Order data

3 Technical data

Model number	8BCM0002.15250-0
General information	
Cable cross section	4x 10 mm ² + (2x 0.75 mm ²)C + (2x 1.5 mm ²)C
Durability	Oil resistance per HD 22.10 appendix A DIN EN 60811-404 ¹⁾
Certification	E170315 cRUus AWM STYLE 21223 AWM I/II A/B 80°C 1000 V FT1 ¹⁾
Certifications	
CE	Yes
UL	cULus E225616 Power conversion equipment
Cable construction	
Power lines	
Quantity	4
Wire insulation	PP
Wire colors	Black, brown, blue, yellow/green
Variant	Tinned copper stranded wire
Cross section	10 mm ²
Shield	No
Stranding	No
Signal line	
Quantity	4
Wire insulation	PP
Wire colors	White, white/red, white/blue, white/green
Variant	Tinned copper stranded wire
Cross section	2x 0.75 mm ² + 2x 1.5 mm ²
Shield	Separate shielding for pairs, tinned copper braiding, optical coverage >85% and foil shield
Stranding	White with white/red and white/blue with white/green
Cable stranding	With filler elements and foil shield
Cable shield	Tinned copper braiding, optical coverage >85% and foil shield
Outer jacket	
Material	TPU
Color	Orange, similar to RAL 2003 flat
Labeling	B&R 4 G 10 + (2x0.75)C + (2x1.5)C C E170315 cRU-us AWM STYLE 21223 AWM I/II A/B 80°C 1000 V FT1 ¹⁾
Connector	
Type	8-pin female speedtec motor connector, size 1.5
Mating cycles	<500
Contacts	8 (4 power and 4 signal contacts)
Additional connectors	8-pin male coupling Connection cycles: <500 Contacts: 8 Degree of protection per EN 60529: IP66/67 when connected
Degree of protection per EN 60529	IP66/67 when connected
Electrical properties ¹⁾	
Operating voltage	Max. 1000 V AC (UL)

Table 2: 8BCM0002.15250-0 - Technical data

Model number	8BCM0002.15250-0	
Test voltage		
Wire/Wire		4 kV
Wire/Shield		4 kV
Conductor resistance		
Power lines		≤2 Ω/km
Signal line		0.75 mm ² : ≤26.7 Ω/km, 1.5 mm ² : ≤13.7 Ω/km
Insulation resistance		≥500 MΩ*km
Current-carrying capacity per DIN VDE 0298 part 4, table 11		
Wall mounting		64.6 A
Installed in conduit or cable duct		54.6 A
Installed in cable tray		68.3 A
Ambient conditions ¹⁾		
Temperature		
Moving		-20°C to +80°C
Static		-20°C to +90°C
Mechanical properties ¹⁾		
Dimensions		
Length		2 m
Diameter		20.1 mm ± 0.4 mm
Bend radius		
Single bend		>62 mm
Moving		>154 mm
Drag chain data		
Acceleration		Max. 50 m/s ² (depends on the length of the travel path)
Flex cycles ²⁾		≥5,000,000
Speed		Max. 300 m/min
Weight		1.1 kg

Table 2: 8BCM0002.15250-0 - Technical data

- 1) Values refer to the raw cable being used.
- 2) At an ambient temperature from -20°C to +60°C.

4 Wiring

4.1 Cable construction

Construction

Pos.	Description	Note
1	Motor line	4x 10 mm ² + 2x 0.75 mm ² + 2x 1.5 mm ²
2	8-pin female circular connector	
3	8-pin male coupling	

Table 3: 10 mm² motor cables - Cable construction

4.2 Pinout

Circular connector	Pin	Description	Function	Coupling
	U	U	Motor connection U	
	Ground symbol	PE	Protective ground conductor	
	W	W	Motor connection W	
	V	V	Motor connection V	
	1	T+	Temperature +	
	2	T-	Temperature -	
	+	B+	Brake +	
	-	B-	Brake -	

Table 4: Pinout

4.3 Cable diagram




Figure 1: 8BCMxxxx.15250-0 - Cable diagram