

**TYPE APPROVAL CERTIFICATE****This is to certify:****That the Peripheral Equipment**with type designation(s)  
**X20-IO Module System Series / 6PPT30 Panel Series**Issued to  
**B&R Industrial Automation GmbH**  
**Eggelsberg, Austria**is found to comply with  
**DNV GL rules for classification – Ships, offshore units, and high speed and light craft****Application :****Product(s) approved by this certificate is/are accepted for installation on all vessels classed by DNV GL.****Location classes:****Temperature B/A\*****Humidity B****Vibration B/A\*****EMC B****Enclosure Required protection according to the Rules shall be provided upon installation on board.****\* see Application/Limitation**This Certificate is valid until **2021-03-20**.Issued at **Hamburg** on **2019-12-13**DNV GL local station: **Augsburg**Approval Engineer: **Heinz Scheffler**for **DNV GL**.....  
**Joannis Papanuskas**  
**Head of Section**

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.

Job Id: **262.1-020756-5**  
Certificate No: **TAA00000BJ**  
Revision No: **5**

## **Product description**

### **Power Supply Modules**

0AC524.9, X20PS2100, X20PS3300, X20PS4951, X20PS9400, X20PS9500, X20PS8002, X20PS9402, X20PS9502, X20PS9600, X20PS9602

### **Terminal Blocks**

0TBxx, X20TBxx

### **Analog Input Modules**

X20AI2632, X20AI2636, X20AI4632, X20AI4636, X20AI2222, X20AI2322, X20AI2437, X20AI2438, X20AI2622, X20AI4222, X20AI4322, X20AI4622, X20AI4632-1, X20AI8221, X20AI8321, X20AI2632-1,

### **Analog Output Modules**

X20AO2622, X20AO2632, X20AO2632-1, X20AO4622, X20AO4632, X20AO4635, X20AO2437, X20AO2438, X20AO4632-1

### **Temperature Modules**

X20AT4222, X20AT2402, X20AT2222, X20AT6402; X20AT2311

### **Bus Base Modules**

X20BB22, X20BB27, X20BB42, X20BB47, X20BB80, X20BB81; X20BB82; X20BB57, X20BB52

### **Bus Controller Modules**

X20BC0043, X20BC0043-10, X20BC0053, X20BC0083, X20BC0087, X20BC0143-10, X20BC1083, X20BC8083, X20BC8084

### **Bus Modules**

X20BM01, X20BM05, X20BM11, X20BM12, X20BM15, X20BM33, X20BM21, X20BM23, X20BM31, X20BM32

### **Universal Mixed Module**

X20CM8281, X20CM0985-1, X20CM2821

### **Compact CPU's**

X20CP0292, X20CP0201, X20CP0291, X20XC0201, X20XC0202, X20XC0292, X20CP0482, X20CP0483, X20CP0484

### **CPU Modules**

X20CP1483, X20CP1483-1, X20CP1484, X20CP1484-1, X20CP1485, X20CP1485-1, X20CP1486, X20CP3484, X20CP3484-1, X20CP3485, X20CP3485-1, X20CP3486, X20CP1583, X20CP1584, X20CP1585, X20CP1586, X20CP3583, X20CP3584, X20CP3585, X20CP3586, X20CP1382-RT, X20CP1301, X20CP1381, X20CP1382, X20CP1381-RT

### **Communication Modules**

X20CS1020, X20CS1030, X20CS1070

### **Counter Modules**

X20DC1176, X20DC1178, X20DC1196, X20DC1198, X20DC11A6, X20DC1376, X20DC137A, X20DC1396, X20DC1398, X20DC1976, X20DC2395, X20DC2396, X20DC2398, X20DC4395

### **Digital Input Modules**

X20DI2371, X20DI2372, X20DI2377, X20DI4371, X20DI4372, X20DI4375, X20DI4760, X20DI6371, X20DI6372, X20DI6373, X20DI8371, X20DI9371, X20DI9372, X20DID371, X20DIF371,

Job Id: **262.1-020756-5**  
Certificate No: **TAA00000BJ**  
Revision No: **5**

**Digital Output Modules**

X20DO2322, X20DO2649, X20DO4322, X20DO4529, X20DO6322, X20DO6529, X20DO8232, X20DO8322, X20DO8332, X20DO9322, X20DOF322, X20DOD322, X20DO4649, X20DO6639, X20DO6325

**Counter and Positioning Modules**

X20DS1119, X20DS1319, X20DS4389

**Hub System Modules**

X20HB1881, X20HB1882, X20HB2880, X20HB2881, X20HB8880, X20HB8884, X20HB8815

**Dummy Modules**

X20IF0000, X20ZF0000

**Interface Modules**

X20IF1020, X20IF1030, X20IF1041-1, X20IF1043-1, X20IF1051-1, X20IF1053-1, X20IF1072, X20IF1074, X20IF1082, X20IF1082-2, X20IF2181-2, X20IF2772, X20IF1061-1, X20IF1063-1; X20IF10A1-1; X20IF10E1-1; X20IF10E3-1; X20IF10D1-1; X20IF10D3-1; X20IF10G3-1; X20IF10H3-1; X20IF10X0

**Motor Bridge Modules**

X20MM2436

**Modules for measure active, reactive and apparent power**

X20AP3111; X20AP3121; X20AP3131; X20AP3161

**Memory Keys**

X20MKxxxx

**Safety CPU Modules (\*1, \*2)**

X20SL8000, X20SL8001, X20SL8010, X20SL8011

**Safety CPU Modules (\*1, \*2)**

X20SL8100, X20SL8101

**Safety Digital Input Modules (\*1, \*2)**

X20SI4100, X20SI2100, X20SI9100

**Safety Digital Output Modules (\*1, \*2)**

X20SO2110, X20SO2120, X20SO4110, X20SO4120

**Safety Analog Input Modules (\*1, \*2)**

X20SA4430, X20ST4492

**Safety Intelligently Programmable Modules (\*1, \*2)**

X20SLX210, X20SLX410, X20SLX910

**Safety Counter and Positioning Module (\*1, \*2)**

X20SD1207

**Safety Digital Mixed Modules (\*1, \*2)**

X20SC2212, X20SC2432

**Power Distribution Modules**

X20PD0011, X20PD0012, X20PD0016, X20PD2113

Job Id: **262.1-020756-5**  
Certificate No: **TAA00000BJ**  
Revision No: **5**

### **CPU Accessory**

0CFCRD.0xxxE.01, 5CFCRD.xxxx-0x

### **Power Panel T-Series 4,3 inch types (\*2)**

6PPT30.043F-20W, 6PPT30.043F-20Cxxx, 6PPT30.043F-20Fxxx, 6PPT30.043F-20Ixxx,  
6PPT30.043F-20B, 6PPT30.043K-20B, 6PPT30.043K-20Fxxx, 6PPT30.043K-20W

### **Power Panel T-Series 5,7 inch types (\*2)**

6PPT30.0573-20B , 6PPT30.0573-20Cxxx, 6PPT30.0573-20Fxxx, 6PPT30.0573-20W,  
6PPT30.057L-20B, 6PPT30.057L-20W

### **Power Panel T-Series 7,2 inch types (\*2)**

6PPT30.0702-20B E, 6PPT30.0702-20Cxxx, 6PPT30.0702-20Fxxx, 6PPT30.0702-20Ixxx,  
6PPT30.0702-20W, 6PPT30.070M-20B, 6PPT30.070M-20Fxxx, 6PPT30.070M-20W

### **Power Panel T-Series 10,1 inch types (\*2)**

6PPT30.101G-20B , 6PPT30.101G-20Cxxx, 6PPT30.101G-20Fxxx, 6PPT30.101G-20W,  
6PPT30.101N-20B, 6PPT30.101N-20W, 6PPT30.101N-20Fxxx, 6PPT30.101N-20Cxxx

## **Application/Limitation**

Location Classes:

- \*1: Environmental category "A" to be cooled inside cabinet.
- \*2: Vibration category "A"

To avoid damages through electrostatic discharge the components have to be mounted inside a control cabinet. All instructions in the User's Manual must be observed and followed in all cases.

At variations of the power supply voltage the User's Manual is to be observed.

The Type Approval covers hardware listed under Product description. When the hardware is used in applications to be classed by DNVGL, documentation for the actual application is to be submitted for approval by the manufacturer of the application system in each case. Reference is made to DNV Rules for Ships Pt.4 Ch.9 Control and Monitoring Systems.

### **Product certificate**

If specified in the Rules, ref. Pt.4 Ch.9 Sec.1, the control and monitoring system in which the above listed hardware is used shall be delivered with a product certificate. For each such delivery the certification test is to be performed at the manufacturer of the application system before the system is shipped to the yard. The test shall be done according to an approved test program. After the certification the clause for application software control will be put into force.

### **Clause for application software control**

All changes in software are to be recorded as long as the system is in use on board. The records of all changes are to be forwarded to DNV for evaluation and approval. Major changes in the software are to be approved before being installed in the computer.

Job Id: **262.1-020756-5**  
Certificate No: **TAA00000BJ**  
Revision No: **5**

## **Type Approval documentation**

**Test reports:** C43857-02-00FT; E43951-00-01JA;; S34471-00-03AV , S34471-00-04AV, S34471-00-05AV, S34470-00-02AV, S4982-00-00JK, E34466-00-01HP, E34467-00-01HP, E34468-00-01HP, E34469-00-01HP, E37149-00-00MU, S37154-00-00AV, E37640-00-01MH, S37155-00-01AV, E38921-01-00HM, C37156-00-00MV, E40222-00-00VK, C40223-00-00MV; C42499-00FT, E42500-00-00AR, C42503-00FT, E42501-00-00AR, C42785-00FT, E42783-00-00JA, BSH Certificate No. 879; BSH Certificate No. 1017; BSH Certificate No. 1018; UL QMFZ8.E148878; UL QMFZ2; C43195-02-00FT; E43194-00-00JA; C44611-00-00FT; E44621-00-00JA; C44612-00-00FT; E44620-00-01JA; C44975-00-00LT; E44971-00-00LC

**Documents:** User's Manual X20 version 3.50; Installation-EMC Guide\_V1.30, Power Panel T30 User`s Manual\_1.42; Marking X20RT8001\_2153931\_29092015.

## **Tests carried out**

Applicable tests according to class guideline DNVGL-CG-0339, November 2016.  
IACS E10, Rev.6 Oct 2014; IEC 60945 (2008), Section 11.2.

## **Marking of product**

The products to be marked with:

- Model name
- Manufacturer name
- Serial number

Coated modules are marking start with the first letter with X20C...

## **Periodical assessment**

The scope of the periodical assessment is to verify that the conditions stipulated for the type are complied with, and that no alterations are made to the product design or choice of systems, software versions, components and/or materials.

The main elements of the assessment are:

- Ensure that type approved documentation is available
- Inspection of factory samples, selected at random from the production line (where practicable)
- Review of production and inspection routines, including test records from product sample tests and control routines
- Ensuring that systems, software versions, components and/or materials used comply with type approved documents and/or referenced system, software, component and material specifications
- Review of possible changes in design of systems, software versions, components, materials and/or performance, and make sure that such changes do not affect the type approval given
- Ensuring traceability between manufacturer's product type marking and the type approval certificate

Periodical assessment is to be performed after 2 years and after 3.5 years. A renewal assessment will be performed at renewal of the certificate.

END OF CERTIFICATE