


# 80CMxx016.77-01 - LinMot hybrid cable

## 1 Order data



Model number	Short description
	<b>LinMot hybrid cable</b>
80CM01016.77-01	ACOPOSmicro LinMot hybrid cable, length 1 m, 4x 0.5 mm <sup>2</sup> + 4x 0.14 mm <sup>2</sup> , 9-pin male DSUB connector on the servo side, 9-pin female Intercontec M17 connector the on motor side, can be used in cable drag chains, UL/CSA listed
80CM02016.77-01	ACOPOSmicro LinMot hybrid cable, length 2 m, 4x 0.5 mm <sup>2</sup> + 4x 0.14 mm <sup>2</sup> , 9-pin male DSUB connector on the servo side, 9-pin female Intercontec M17 connector the on motor side, can be used in cable drag chains, UL/CSA listed
80CM03016.77-01	ACOPOSmicro LinMot hybrid cable, length 3 m, 4x 0.5 mm <sup>2</sup> + 4x 0.14 mm <sup>2</sup> , 9-pin male DSUB connector on the servo side, 9-pin female Intercontec M17 connector the on motor side, can be used in cable drag chains, UL/CSA listed
80CM05016.77-01	ACOPOSmicro LinMot hybrid cable, length 5 m, 4x 0.5 mm <sup>2</sup> + 4x 0.14 mm <sup>2</sup> , 9-pin male DSUB connector on the servo side, 9-pin female Intercontec M17 connector the on motor side, can be used in cable drag chains, UL/CSA listed
80CM10016.77-01	ACOPOSmicro LinMot hybrid cable, length 10 m, 4x 0.5 mm <sup>2</sup> + 4x 0.14 mm <sup>2</sup> , 9-pin male DSUB connector on the servo side, 9-pin female Intercontec M17 connector the on motor side, can be used in cable drag chains, UL/CSA listed
80CM15016.77-01	ACOPOSmicro LinMot hybrid cable, length 15 m, 4x 0.5 mm <sup>2</sup> + 4x 0.14 mm <sup>2</sup> , 9-pin male DSUB connector on the servo side, 9-pin female Intercontec M17 connector the on motor side, can be used in cable drag chains, UL/CSA listed
80CM20016.77-01	ACOPOSmicro LinMot hybrid cable, length 20 m, 4x 0.5 mm <sup>2</sup> + 4x 0.14 mm <sup>2</sup> , 9-pin male DSUB connector on the servo side, 9-pin female Intercontec M17 connector the on motor side, can be used in cable drag chains, UL/CSA listed

Table 1: 80CM01016.77-01, 80CM02016.77-01, 80CM03016.77-01, 80CM05016.77-01, 80CM10016.77-01, 80CM15016.77-01, 80CM20016.77-01 - Order data

## 2 Technical data

Model number	80CM01016.77-01	80CM02016.77-01	80CM03016.77-01	80CM05016.77-01	80CM10016.77-01	80CM15016.77-01	80CM20016.77-01
<b>General information</b>							
Cable cross section	4x 0.14 mm <sup>2</sup> + 4x 0.5 mm <sup>2</sup>						
<b>Cable construction</b>							
Power lines							
Quantity	8						
Wire insulation	TPE						
Wire colors	0.14 mm <sup>2</sup> : White, black, green, yellow; 0.5 mm <sup>2</sup> : Red, pink, blue, gray						
Design	0.14 mm <sup>2</sup> tinned copper braid						
Cross section	0.14 mm <sup>2</sup> and 0.5 mm <sup>2</sup>						
Shield	Tinned copper braid						
Stranding	Wires braided in layers						
Cable stranding	Via inner element (4x 0.14 mm <sup>2</sup> ) C wires 0.5 mm <sup>2</sup> optimally braided in layers						
Complete shielding	Tinned copper braid						
Outer jacket							
Material	PUR						
Color	Jet black						
Labeling	Linear motor cable KS05						
<b>Electrical characteristics</b>							
Test voltage							
Wire/Wire	2000 V						
Wire/Shield	1200 V						
<b>Mechanical characteristics</b>							
Dimensions							
Length	1 m	2 m	3 m	5 m	10 m	15 m	20 m
Diameter	9.5 mm						
Bend radius							
Single bend	5x wire diameter						
Moving	10x wire diameter						
Can be used in cable drag chains	Yes						

Table 2: 80CM01016.77-01, 80CM02016.77-01, 80CM03016.77-01, 80CM05016.77-01, 80CM10016.77-01, 80CM15016.77-01, 80CM20016.77-01 - Technical data

### 3 Wiring

#### 3.1 Pinout

Position	Quantity	Description
1	1	Motor line (Cable diameter: 9.5 mm) (4x 0.5 mm <sup>2</sup> ) (4x 0.14 mm <sup>2</sup> )
2	1	Cable shield covered with heat shrink tubing: Color: Yellow/Green
4	1	DSUB
5	1	Heat shrink tubing
6	5	Wire end sleeve
8	1	Heat shrink tubing
9	1	9-pin connection

Table 3: Components

Connection	Pin	Description	Color	Function	Pin	Connection
	1	Ph1+	Red	Motor connection Ph1+		
	2	Ph1-	Pink	Motor connection Ph1-		
	3	Ph2+	Blue	Motor connection Ph2+		
	4	Ph2-	Gray	Motor connection Ph2-		
	A	+5 VDC	White	Encoder power supply 5 V	1	
	B	AGND	Inner shield	Encoder power supply 0 V	6	
	C	+Sin	Yellow	Sine	2	
	D	+Cos	Green	Cosine	5	
	E	Temperature	Black	TEMP	8	
	Jacket		-	External shield		

Table 4: Pinout

### 3.2 Cable diagram




Table 5: Cable diagram