

8BCF0030.1221B-0

1 General information

- Can be used in cable drag chains
- Assembled specifically for use with ACOPOSmulti drive systems and B&R servo motors with series 615 built-in connectors
- itec - Innovative connector system for fast and secure connections

2 Order data


Model number	Short description	Figure
8BCF0030.1221B-0	EnDat 2.2 cables EnDat 2.2 cable, length 30 m, 1x 4x 0.14 mm ² + 4x 0.35 mm ² , 12-pin female series 615 signal connector, 9-pin male DSUB servo connector, can be used in cable drag chains	

Table 1: 8BCF0030.1221B-0 - Order data

3 Technical data

Model number	8BCF0030.1221B-0
General information	
Cable cross section	4x 0.14 mm ² + 4x 0.35 mm ²
Durability	Oil resistance per DIN EN 50363-10-2 (VDE 0207-363-10-2) as well as standard cleaning agents and hydraulic oil ¹⁾
Certification	UL AWM Style 20963, 80°C, 30 V, E63216 ¹⁾
Certifications	
CE	Yes
Cable construction	
Supply lines	
Quantity	4
Wire insulation	Special thermoplastic material
Wire colors	White/Green, brown/green, blue, white
Variant	Tinned copper stranded wire
Cross section	0.35 mm ²
Shield	No
Stranding	No
Signal line	
Quantity	4
Wire insulation	Polyolefin foam
Wire colors	Yellow, gray, pink, violet
Variant	Tinned copper stranded wire
Cross section	0.14 mm ²
Shield	No
Stranding	All 4 wires together
Cable stranding	With terminating foil shield
Cable shield	Copper/Tin braiding, optical coverage ≥85%
Outer jacket	
Material	PUR
Color	Green flat
Labeling	B&R 4x0,14 + 4x0,35 FLEX (UL) AWM STYLE 20963 80°C 30 V E63216 ¹⁾
Connector	
Type	12-pin female series 615 signal connector
Mating cycles	<500
Contacts	12
Additional connectors	9-pin male DSUB servo connector Mating cycles: <200 Contacts: 9 Degree of protection per EN 60529: IP20 when connected
Degree of protection per EN 60529	IP66/67 when connected
Electrical properties ¹⁾	
Operating voltage	≤30 V

Table 2: 8BCF0030.1221B-0 - Technical data


Model number	8BCF0030.1221B-0
Test voltage	
Wire - Wire	1 kV
Wire - Shield	0.5 kV
Conductor resistance	
Supply lines	≤55 Ω/km
Signal line	≤134 Ω/km
Insulation resistance	>200 MΩ*km
Ambient conditions ¹⁾	
Temperature	
Moving	-20°C to +80°C
Static	-20°C to +80°C
Mechanical properties ¹⁾	
Dimensions	
Length	30 m
Diameter	6 mm ±0.2 mm
Bend radius	
Single bend	≥19 mm
Moving	≥47 mm
Drag chain data	
Acceleration	≤6 g
Flex cycles ²⁾	≥3000000
Velocity	≤4 m/s
Weight	1.74 kg

Table 2: 8BCF0030.1221B-0 - Technical data

- 1) Values refer to the raw cable being used.
- 2) Valid at an ambient temperature of 20°C and bend radius of 78 mm.

4 Wiring

4.1 Construction



Pos.	Description	Note
1	Encoder cable	4x 0.14 mm ² + 4x 0.35 mm ²
2	Circular connector, 12-pin female	
3	Heat shrink tubing	
4	DSUB housing 45°, metal-plated, 9-pin connector	

Table 3: 8BCF EnDat 2.2 cables - Construction

4.2 Pinout



Circular connector	Pin	Description	Function	Pin	DSUB connector
	1	+12 V out	Encoder power supply +12 V	1	
	2	D	Data input	4	
	3	D\	Data inverted	8	
	4	T	Clock output	5	
	5	T\	Clock output inverted	9	
	6	Batt COM	Battery backup 0 V	7	
	7	COM	Encoder power supply 0 V	6	
	8	---	Coding contact		
	9	---			
	10	---			
	11	---			
	12	Vbatt	Battery backup power supply	2	

Table 4: 8BCF EnDat 2.2 cables - Pinout

4.3 Cable diagram




Figure 1: 8BCF EnDat 2.2 cables - Cable diagram